



Which one should I choose?

The 9PX 2 and 3 kVA UPS models are here—reliable, versatile, powerful, efficient power for IT equipment. If you're looking to upgrade your 9130 UPS, here are your best bets.

9PX – 2 kVA 120V

| Spec | 9130 2K RM 120V | 9PX 2K RT 120V |
|--------------------------------|--------------------------|--------------------------|
| Part number | PW9130L2000R-XL2U | 9PX2000RT |
| VA | 2000 | 2000 |
| Watts | 1800 | 1800 |
| Runtime (1800W) | 6.0 | 6.0 |
| Efficiency | 88% at full load | 91.4% at full load |
| ENERGY STAR | No | Yes |
| Input plug | 5-20P | 5-20P |
| Input cord length | 6 feet | 8 feet |
| Receptacles | (6) 5-20R, (1) L5-20R | (6) 5-20R, (1) L5-20R |
| Form factor | Rackmount only | Rack/Tower |
| Dimensions (HxWxD, in.) | 3.4 (2U) x 17.3 x 22.6 | 3.4 (2U) x 17.3 x 23.8 |
| Weight | 63.9 | 61.5 |
| Interface | Two-line graphical LCD | Multi-line graphical LCD |
| NIC | Network-MS | Network-MS |
| Communications port | BD-Slot (XCP) | MS (SHUT) |
| ABM | Yes | Yes |



9PX2000RT rear view



Powering Business Worldwide

9PX – 3 kVA 120V

| Spec | 9130 3K RM 120V | 9PX 3K RT 120V |
|-------------------------|------------------------|--------------------------|
| Part number | PW9130L3000R-XL2U | 9PX3000RT |
| VA | 3000 | 3000 |
| Watts | 2700 | 2700 |
| Runtime (2700W) | 3.3 | 3.7 |
| Efficiency | 90% at full load | 91.6% at full load |
| ENERGY STAR | No | Yes |
| Input plug | L5-30P | L5-30P |
| Input cord length | 6 feet | 8 feet |
| Receptacles | (6) 5-20R, (1) L5-30R | (6) 5-20R, (1) L5-30R |
| Form factor | Rackmount only | Rack/Tower |
| Dimensions (HxWxD, in.) | 3.4 (2U) x 17.3 x 22.6 | 3.4 (2U) x 17.3 x 23.8 |
| Weight | 63.9 | 63.1 |
| Interface | Two-line graphical LCD | Multi-line graphical LCD |
| NIC | Network-MS | Network-MS |
| Communications port | BD-Slot (XCP) | MS (SHUT) |
| ABM | Yes | Yes |



9PX3000RT rear view

9PX – 2 kVA 230V

| Spec | 9130 2K RM 230V | 9PX 2K G RT 230V |
|-------------------------|------------------------|--------------------------|
| Part number | PW9130i2000R-XL2U | 9PX2200GRT |
| VA | 2000 | 2200 |
| Watts | 1800 | 2000 |
| Runtime (1800W) | 6.0 | 6.0 |
| Efficiency | 90% at full load | 92.9% at full load |
| ENERGY STAR | No | Yes |
| Input plug | C20 | C20 / L6-20P |
| Input cord | — | C19 to L6-20P |
| Input cord length | — | 6 feet |
| Receptacles | (1) C19, (8) C13 | (2) C19, (8) C13 |
| Form factor | Rackmount only | Rack/Tower |
| Dimensions (HxWxD, in.) | 3.4 (2U) x 17.3 x 22.6 | 3.4 (2U) x 17.3 x 23.8 |
| Weight | 63.9 | 60.4 |
| Interface | Two-line graphical LCD | Multi-line graphical LCD |
| NIC | Network-MS | Network-MS |
| Communications port | BD-Slot (XCP) | MS (SHUT) |
| ABM | Yes | Yes |

9PX – 3 kVA 230V

| Spec | 9130 3K i RM 230V | 9130 3K G RM 230V | 9PX 3K G RT 230V |
|-------------------------|------------------------|------------------------|--------------------------|
| Part number | PW9130L3000R-XL2U | PW9130G3000R-XL2UEU | 9PX3000GRT |
| VA | 3000 | 3000 | 3000 |
| Watts | 2700 | 2700 | 3000 |
| Runtime (2700W) | 3.3 | 3.3 | 3.7 |
| Efficiency | 91% at full load | 91% at full load | 93.7% at full load |
| ENERGY STAR | No | No | Yes |
| Input plug | C20 | C20 / L6-20P | C20 / L6-20P |
| Input cord | C19 to C20 | C19 to L6-20P | C19 to L6-20P |
| Input cord length | 6 feet | 6 feet | 6 feet |
| Receptacles | (1) C19, (8) C13 | (1) C19, (8) C13 | (2) C19, (8) C13 |
| Form factor | Rackmount only | Rackmount only | Rack/Tower |
| Dimensions (HxWxD, in.) | 3.4 (2U) x 17.3 x 22.6 | 3.4 (2U) x 17.3 x 22.6 | 3.4 (2U) x 17.3 x 23.8 |
| Weight | 63.9 | 63.9 | 60.4 |
| Interface | Two-line graphical LCD | Two-line graphical LCD | Multi-line graphical LCD |
| NIC | Network-MS | Network-MS | Network-MS |
| Communications port | BD-Slot (XCP) | BD-Slot (XCP) | MS (SHUT) |
| ABM | Yes | Yes | Yes |



9PX2200GRT and 9PX3000GRT rear view

9PX – 3 kVA locking outlet 230V

| Spec | 9130 3K RM 230V | 9PX 3K GL RT 230V |
|-------------------------|------------------------|--------------------------|
| Part number | PW9130G3000R-XL2U | 9PX3000GLRT |
| VA | 3000 | 3000 |
| Watts | 2700 | 3000 |
| Runtime (2700W) | 3.3 | 3.7 |
| Efficiency | 91% at full load | 93.7% at full load |
| ENERGY STAR | No | Yes |
| Input plug | C20 / L6-20P | C20 / L6-20P |
| Input cord | C19 to L6-20P | C19 to L6-20P |
| Input cord length | 6 feet | 6 feet |
| Receptacles | (1) L6-30R, (2) L6-20R | (1) L6-30R, (2) L6-20R |
| Form factor | Rackmount only | Rack/Tower |
| Dimensions (HxWxD, in.) | 3.4 (2U) x 17.3 x 22.6 | 3.4 (2U) x 17.3 x 23.8 |
| Weight | 63.9 | 60.4 |
| Interface | Two-line graphical LCD | Multi-line graphical LCD |
| NIC | Network-MS | Network-MS |
| Communications port | BD-Slot (XCP) | MS (SHUT) |
| ABM | Yes | Yes |

9PX 2-3 kVA EBM

| Spec | 9130 EBM 2-3K RM 120V | 9PX EBM 2-3K RT 120V |
|-------------------------|------------------------|------------------------|
| Part number | PW9130L3000R-EBM2U | 9PXEBM72RT |
| Dimensions (HxWxD, in.) | 3.4 (2U) x 17.3 x 22.6 | 3.4 (2U) x 17.3 x 23.8 |
| Weight | 90.6 | 86.4 |
| EBM cross compatible | No | No |



Eaton 9PX 2 and 3 kVA models work in tower or rack formats. The easy-to-read graphical LCD displays UPS status, analytics and enhanced configuration capabilities.



The LCD screen and logo rotate to match your selected configuration.



Easy-to-remove battery trays make battery replacement a breeze.



Add up to four extended battery modules for even more runtime.

For more information and to interact with the 9PX, visit Eaton.com/9PX

Eaton
 1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
 Eaton.com

© 2016 Eaton
 All Rights Reserved
 Printed in USA
 Publication No. CC153009EN / GG
 June 2016



Eaton is a registered trademark.
 All other trademarks are property of their respective owners.